



New!!!


D80S



**New design,
same functions**



- Connection of 8 capacitive Sylvac probes *
- Graphic display at the tenth of a micron, with back light
- RS232-C output
- Analog output
- etc...



* with unit D108




New!!!


D80S: Flexibility of use and conviviality at the production's service **804.1080**



Resolution up to 0.0001mm



Easy editing of the tolerance




Dynamic functions



Luminous display of the tolerance



Analog outputs



Changes without prior notice
Represented by:



SYLVAC SA CP Ch. du Closalet 16 CH-1023-Crissier

Tél: +41 (0) 21 637 67 57 Fax: +41 (0) 21 637 67 40

E-mail: sales@sylvac.ch

Web: www.sylvac.ch